

FI-75

Rugged & Reliable Automatic X-Ray Film Processor *The Standard of Excellence in 90 Second Processing*



The FI-75 is the world's premier 90 second automatic x-ray film processor. Designed as a rugged workhorse, the FI-75 can handle film volumes from very low to a higher capacity

The proven design of the FI-75 is efficient with energy, water and chemical use, saving the FI-75 owner money while delivering outstanding quality images.

The FI-75 is manufactured in Germany in compliance with DIN ISO 9001:2000, IEC, TUV, CE, CSA, and UL quality standards. The FI-75 sets the standard of excellence for 90 second automatic x-ray film processors.

Features & Benefits

- Lightweight yet rugged tabletop processor
- 90 second processing speed, leading edge to leading edge
- Energy and water saving design limits run time to when film is actually being processed
- Anti-oxidation and anti-crystallization programs result in chemical savings and outstanding image quality
- Intelligent replenishment sensor limits chemical use resulting in chemical savings
- All components are easily accessible underneath for service
- Temperature control on the front panel for ease of use
- Top film feed and top return for convenience
- Film transport rack design with spring loaded rollers helps eliminate film jam problems found with other brands
- Quality polyurethane & rubber rollers for outstanding image quality and no artifacts
- 2 year warranty
- Meets ISO, IEC, CE, TUV, CSA & UL quality standards
- Made in Germany

Standard Equipment

- Comes complete and ready with all components for tabletop processing
- Levelling legs for uneven surfaces
- Spare parts kit
- 6.6 gallon (25 liter) replenishment tanks with filtering replenishment straws
- Floating lid for developer tank
- Water supply hose
- Tubing and hardware
- Installation, Operating and Parts Manual

Options

- 220V, 50/60Hz service for international
- Basic or Deluxe stands
- 10 gallon (38 liter) replenishment tanks
- No Plumbing Kit for closed loop operation
- Thru-the-wall construction
- Silver recovery bucket
- Chemical mixer



FI Sales, LLC[®]

761 N. 17th St., #17
St. Charles, IL 60174 USA
(630) 444-1380 Fax: (630) 444-1381

Visit FI Sales online at
www.fisalesllc.com or
sales@fisalesllc.com

FI-75

Rugged X-Ray Film Processor

Minimum Darkroom Requirements

Electrical

- 115V, 50/60Hz, 15A Service (Operating Range 110-120V)
- 230V, 50/60Hz, 10A Service (Operating Range 220-240V)
- Energy use of 1.4 kWh during processing and 0.12 kWh in standby mode.
- Dedicated line strongly recommended.
- Use of a multi-outlet adapter or extension cord will void the warranty.

Water

- Cold water only with recommended temperature between 41-78°F (5-26°C).
- Water connection of 3/4" with 29 - 145 psi (2 - 10 bar).
- Minimum drain diameter of 2 inches (5 cm) at a maximum of 12 inches (30.5 cm) above the floor.
- Water consumption of 0.50 gal/min (1.9 liter/min) during processing.
- Water consumption of 0.0 gal/min (0.0 l/min) in standby mode.
- In-line water filter strongly recommended when water supply contains contaminants or particulate materials.
- Do not use copper drain pipe or fittings. Use cast iron or PVC.

Space

- Actual dimensions 30" (77 cm) long by 23" (59 cm) wide by 16.5" (42 cm) tall.
- Please allow adequate clearance on sides, back and top of processor for ease of use, maintenance and service.



FI-75 shown installed for thru-the-wall use

Film Processing Capacity Measured at 90 Second Processing Speed

10" X 12" (24 X 30 cm), 129 films per hour

14" X 17" (35 X 43 cm), 75 films per hour

PRODUCT SPECIFICATIONS

• Film Size

4" x 4" (10 cm x 10 cm) min. to
17" (43 cm) X any length max.
Will accept roll film

• Processing Time

90 seconds (factory set),
leading edge to leading edge

• Developer Temp

82-99 °F (28-37°C), adjustable

• Replenishment

Rates adjustable either
450 ml per 10 sq. ft. (ml/m²) or
600 ml per 10 sq. ft. (ml/m²)
Manual pumping selection
allows for automatic fill of the
internal chemical tanks

• Net Weight (Empty/Filled)

77/110 lbs (35/50 kg)

• Tank Capacity

1.3 gallons (5.0 liters) in each
section: developer, fixer, water

• Film Drying

Warm circulated air, factory set
to 149°F (65°C)


• Chemical Storage

6.6 gallon (25 L) tanks
10 gallon (38 L) tanks optional

• Film & Chemistry

Use standard medical x-ray film
and chemistry formulated for
automatic medical x-ray film
processors.

Your Authorized FI Sales, LLC Dealer



FI Sales is pleased to offer other x-ray film processors should the FI-75 not meet your needs.

- FI-45 World's most economical processor with 100 second processing
- FI-VS 90 second variable speed model
- FI-245 Deep tank floor model for high capacity film processing



© 2008 FI Sales, LLC