

# INSTA-VELOPER PORTABLE DARKROOM

INSTA-VELOPER ... A new age of flexibility and convenience in X-ray processing has arrived. The INSTA-VELOPER enables quality processing to be completed chairside, under normal office lighting, in just seconds with Insta-Neg and Insta-Fix.



**FI Sales, LLC®**

761 N. 17th St., #17  
St. Charles, IL 60174 USA  
(630) 444-1380 Fax: (630) 444-1381

Visit FI Sales, LLC online at  
[www.fisalesllc.com](http://www.fisalesllc.com)  
or email us at  
[sales@fisalesllc.com](mailto:sales@fisalesllc.com)

# INSTA-VELOPER PORTABLE DARKROOM

Now you can have —  
**INSTANT CHAIRSIDE X-RAYS IN SECONDS!**

✓ **CUT TREATMENT TIME DRASTICALLY.**

- Process X-rays in less than 30 seconds at normal room temperature under normal office lighting. What a time-saver and patient-pleaser!
- Free-up busy darkrooms and automatic processors.
- The INSTA-VELOPER is a great back-up system, too!

✓ **QUALITY X-RAYS AT A FRACTION OF THE COST.**


- No large outlay for expensive equipment or expensive film.
- Compared to similar systems, the INSTA-VELOPER is economical in use and the quality of design and craftsmanship far superior.
- Consider, for example, the exclusive feature of hermetic solution containers in the INSTA-VELOPER: Quick and clean air-tight covers effectively control oxidation—reducing solution costs considerably.

✓ **SO EASY TO USE — IT'S FOOLPROOF.**

- No heating of solutions. Electricity and plumbing are not required.
- All parts are chemical resistant, with no moving parts to breakdown.
- The INSTA-VELOPER is amazingly simple to use, extremely reliable and—best of all—easy to maintain!



Complete processing of intraoral film, from removal of film jacket to final rinse, is performed within the light-tight unit. Top viewing panel lifts back for removal of processed film.



Attractive light Oyster Grey exterior finish/Charcoal interior.  
Overall Dimensions 15¼" x 10½" x 10" high

## FEATURES OF THE INSTA-VELOPER

- EASY SEE-THROUGH (AMBER) LIGHT-FILTERING PANEL**
  - Completely filters out normal office lighting. Effective for all brands of intraoral film, including Kodak Ultra and Ektaspeed.
  - Tilts back into recessed hinge for entry from above.
- STURDY MOLDED STRUCTURAL PLASTIC COVER**
  - Time/Temp. processing chart on top for convenient reference.
  - Front contoured for normal arm positioning.
  - Dark-colored interior reduces chance of film-fogging by minimizing inside reflected light.
  - Interior channels for hanging extra film clips.
- UNIQUE HAND-ENTRY WRIST 'GRIPS'**
  - Interwoven nylon reinforced neoprene 'grips' allow easy hand entry, yet effectively grip both large and small wrists—preventing harmful light entry.
  - Extremely durable—easily removable—washable.
- DETACHABLE MOLDED STRUCTURAL PLASTIC BASE**
  - Easily removable for convenient interior cleaning.
  - Recessed retainers securely hold processing containers.
  - Recessed front tray for discarded film jackets.
- HERMETIC-SEALING DEVELOPER & FIXER CONTAINERS (2)**
  - Exclusive feature: 8 oz. containers are equipped with easy-to-open/close stainless steel gasketed closures which effectively control solution oxidation.
- RINSE WATER CONTAINERS with transport caps (2)**
- Velcro® Fasteners (4) for securing unit to countertop.**  
(Supplied in addition to rubber anti-slip pads. Use is optional.)

The INSTA-VELOPER was designed for use with our rapid X-ray processing solutions:

### INSTA-NEG/INSTA-FIX™ X-RAY PROCESSING CHART

Temp.	18° 64°	20° 68°	22° 72°	25° 76°	27° 80°	29° 84°	C°	F°
Develop.	30	23	16	12	9	8		seconds
Fix	60	45	30	25	20	20		seconds

**Instant Processing.** Completely develop and fix X-rays in less than 60 seconds at normal room temperature! Extra-rapid 'working' films are processed in 15-30 seconds. INSTA-NEG Developer gives both speed and quality with results equal to conventional processing. After the X-ray film is developed and immersed in water a few seconds it is ready for INSTA-FIX which **permanently** fixes film in 15-30 seconds. Archival quality film—*without* fading, browning or yellowing—is achieved following final wash.

**Economical.** Even if it takes weeks or months, with INSTA-NEG & INSTA-FIX 60-100 film can be processed per filling of the hermetic-sealing containers in the INSTA-VELOPER. Solutions are premixed, packaged in quarts and gallons.



**FI Sales, LLC®**

761 N. 17th St., #17  
St. Charles, IL 60174 USA  
(630) 444-1380 Fax: (630) 444-1381

Visit FI Sales, LLC online at  
[www.fisalesllc.com](http://www.fisalesllc.com)  
or email us at  
[sales@fisalesllc.com](mailto:sales@fisalesllc.com)